

8-Axis Quantum^M FaroArm[®] / ScanArm V2

Excellent Price/Performance Ratio for High-End Factory Inspection



The FARO® 8-Axis Quantum^M FaroArm® V2 offers a comprehensive, contact/ non-contact metrology solution, allowing users to significantly speed up and simplify their measurement and scanning activities. The system provides rapid data capture, superior resolution and high accuracy. It is ideal for inspection and quality control, offering a perfect solution for point cloud comparison with CAD, rapid prototyping, reverse engineering and 3D modeling of free-form surfaces. The FARO 8-Axis Quantum^M ScanArm V2 combines a Quantum^M FaroArm V2, a FAROBlu® or PRIZM™ Laser Line Probe, and an 8-Axis Scanning Platform; making it the first and only eight-axis portable metrology solution available in the marketplace!

The FAROBlu LLP uses best-in-class blue laser technology, providing the highest accuracy point cloud data with unparalleled non-contact measurement capabilities at high speed.

The FARO PRIZM LLP represents a great value, utilizing green laser technology to deliver high fidelity color scanning and allows users to view, inspect and manipulate detail-rich, true color point clouds of parts or assemblies.

Both the FAROBlu and PRIZM, Quantum ScanArms, are certified according to ISO 10360-8 for non-contact CMMs. FARO was the first portable measurement arm manufacturer to publish its non-contact accuracy specifications according to this standard.

FAROBlu and PRIZM Features

Blue and Green Laser

The FAROBlu LLP leverages blue laser technology which has a shorter wavelength than red or green lasers and delivers improved scanning results with higher fidelity. This means smaller details are captured, along with a vast improvement of the scan-ability of dark and shiny surfaces. When the highest precision is a must, only the FAROBlu will do.

The PRIZM LLP takes advantage of green laser technology. This wavelength is superior to red lasers by producing less speckle and resulting in greater detail. Green lasers are best suited to provide visual color definition, delivering full-spectrum color scanning capabilities for high-resolution color point cloud data capture and analysis. Additionally, users can switch to grayscale or monochromatic modes, which provide options for faster scanning rates. The PRIZM offers a great balance of speed and accuracy, with the added benefit of color scanning.

Laser Line Width

The FAROBlu and PRIZM LLPs feature a laser line width of 150mm. The extensive line width scans a larger area, delivering fast and efficient scanning.

Advanced Sensor

The FAROBlu and PRIZM LLP cameras use the most advanced CMOS technology to deliver incredibly fast frame rates (the number of times per second that the camera gathers new data on the part being scanned).

Ergonomics

Designed with ergonomics in mind, our LLPs are aligned with natural wrist position in mind. The natural position of the wrist is similar to the way you hold a coffee mug or hammer, and the intuitive scanning flow is left to right (not top to bottom). FARO has designed the scanning beam to be vertically oriented to minimize fatigue and drive scanning efficiency.

8-Axis Features

An industry exclusive, the integrated 8-Axis rotary scanning platform decreases scan time up to 40%, while maintaining accuracy. Rotate the part to you, with the ultimate CMM system available today. The 8-Axis unit is available with all Quantum models.

Benefits

Fast Scanning Speed

The extra-wide scan stripe and fast frame rate boost productivity by increasing coverage and reducing scanning time. Combined with the 8-Axis rotation of objects in real-time, the scanning process itself is even faster.

High-Definition Data

Intricate components can be captured in fine detail as a result of dense point data on each scanline.

Scan Challenging Materials

Seamlessly scan across diverse surface materials regardless of contrast, reflectivity or part complexity without any special coatings or target placement.

Color Scanning

High resolution, 3D color scanning for vivid, real-world visualization and CAD reconstruction of parts and assemblies with the FARO PRIZM Laser Line Probe.

Specifications

Contact Measurement (Arm)*										
Measurement Range	SPAT ¹		E _{UNI} ²		Psize ³		PFORM ⁴		L _{DIA} ⁵	
Quantum ^M V2	6 Axis	7 Axis	6 Axis	7 Axis	6 Axis	7 Axis	6 Axis	7 Axis	6 Axis	7 Axis
2.5 m	0.023 mm	0.027 mm	0.030 mm	0.032 mm	0.013 mm	0.013 mm	0.023 mm	0.026 mm	0.038 mm	0.049 mm
3.0 m	0.034 mm	0.042 mm	0.042 mm	0.054 mm	0.016 mm	0.020 mm	0.032 mm	0.036 mm	0.052 mm	0.080 mm
3.5 m	0.044 mm	0.055 mm	0.056 mm	0.066 mm	0.020 mm	0.024 mm	0.039 mm	0.043 mm	0.068 mm	0.096 mm
4.0 m	0.053 mm	0.065 mm	0.067 mm	0.082 mm	0.024 mm	0.029 mm	0.044 mm	0.048 mm	0.084 mm	0.118 mm

Non-C	Contact Measurement (Scan	8-Axis System**				
Measurement Range	System Accuracy ⁶					
Quantum ^M V2	FAROBlu HD	PRIZM	6 Axis	7 Axis		
2.5 m	0.046 mm	0.051 mm	0.038 mm	0.049 mm		
3.0 m	0.062 mm	0.067 mm	0.052 mm	0.080 mm		
3.5 m	0.076 mm	0.081 mm	0.068 mm	0.096 mm		
4.0 m	0.088 mm	0.093 mm	0.084 mm	0.118 mm		

All values represent MPE (Maximum Permissible Error)

¹ SPAT – Single Point Articulation Test | ² E_{UNI} – Distance Error between two points comparing measured versus nominal values | ³ P_{SIZE} – Sphere Probing Size Error comparing measured versus nominal values | ⁴ P_{FORM} – Sphere Probing Form Error | ⁵ L_{DIA} – Sphere Location Diameter Error (Diameter of the spherical zone containing the centers of a sphere measured from multiple orientations) | ⁶ System Accuracy – Based on Sphere Location Diameter Error

Laser Line Probe Specifications						
	FAROBlu HD	FARO PRIZM Color				
Accuracy	±25 μm	±30 µm				
Repeatability	25 μm, 2σ	30 μm, 2σ				
Stand-off	115 mm					
Depth of field	115 mm					
Effective scan width	Near field 80 mm; Far field 150 mm					
Points per line	Maximum 4,000 points/line					
Minimum point spacing	20 μm					
Scan rate	Maximum 600 Hz	Maximum 300 Hz				
	Points per second					
Point acquisition rate	Up to 1.2 million	Color: 240,000 Grayscale: 240,000 Monochromatic: 1.2 million				
Laser	Class 2					
Weight	485 g					

Accuracy and repeatability specified at Full Field of View (FOV)

Arm Hardware Specifications

FaroArm weight (range): 8.5kg to 9.3kg

3.0Kg

Operating temp range: 10°C - 40°C
Temperature rate: 3°C/5 min

Operating humidity range: 95%, non-condensing

Power supply: Universal worldwide

voltage; 100-240 VAC;

47/63 Hz

8-Axis Hardware Specifications

Max operating weight: 100kg

Rotary plate size options: 250 mm / 500 mm

Meets OSHA requirements, NRTL TÜV SÜD C-US Listed, Complies with Electronic Code of Federal Regulations 47 CFR PART 15, 17 CFR Parts 240 and 249b – Conflict Material, 21 CFR 1040 Performance standards For Light-Emitting Products, and 10 CFR Part 430 – Department of Energy; Energy Conservation for External Power Supplies

Complies with the following EC Directives: 93/68/EEC CE Marking; 2014/30/EU Electrical Equipment; 2014/53/EU Radio Equipment Directive; 2011/65/EU RoHS2; 2002/96/EC WEEE; 2006/66/EC Batteries and Accumulators; 2014/35/EU Low Voltage Directive; 2009/125/EC Ecodesign requirement. Conforms to the following standards: EN 61010-1:2010 / CSA-C22.2 No. 61010-1; EN 61326-1:2013 EMC; ETSI EN 300 328 V2.1.1; ETSI 301 489-1 V1.9.2; ETSI 301 489-17 V2.2.1; ETSI EN 62311:2008; IEEE 802.11 b/g; FCC Part 15.247 (WLAN and Bluetooth); Japanese Radio Law MPT No. 37 Ordinance (MIC classification WW); UN T1-T8; IEC 62133 2nd ed.; IEC 60825-1:2014 ed3.0; FDA (CDRH) 21 CFR 1040.10 / ANSI Z136.1-2007; EN 50581:2012; 21 CFR 1002 (Records & Reports); 21 CFR 1010 (Performance Standards).

Shock and Vibrations Testing per International Electrotechnical Commission (IEC) Standards: IEC 60068-2-6; IEC 60068-2-64; IEC 60068-2-27 Extreme Temperature Cycling (-20°C to 60°C). Based on: IEC 60068-2-1; MIL-STD-810G; ISTA



IB-CADDY D.O.O.
Dunajska cesta 106
1000 Ljubljana
tel.:(0)1 566 12 55
info@ib-caddy.com
www.ib-caddy.com



^{*}Contact Measurement (Arm): In accordance with ISO 10360-12 | **8-Axis System (Arm + 8-Axis): Full system performance based on ISO10360-12 Sphere Location Diameter Error (L_{DIA}) | ***Non-Contact Measurement (ScanArm and ScanArm + 8-Axis): Full System performance based on ISO 10360-8 Annex D